




## FSR24-5/8"-13MM-SS

Ruland FSR24-5/8"-13MM-SS, 5/8" x 13mm Six Beam Coupling, Stainless Steel, Set Screw Style, 1.500" (38.1mm) OD, 2.250" (57.2mm) Length





## **Description**

Ruland FSR24-5/8"-13MM-SS is a set screw style six beam coupling with 0.6250" x 13mm bores, 1.500" (38.1mm) OD, and 2.250" (57.2mm) length. It is machined from a single piece of material and features two sets of three spiral cuts. This gives it higher torque capacity, lower windup, and larger body sizes than single or four beam couplings and allows for use in light duty power transmission applications such as coupling a servo motor to a lead screw. FSR24-5/8"-13MM-SS is zero-backlash and has a balanced design for reduced vibration at high speeds of up to 6,000 RPM. All hardware is metric and tests beyond DIN 912 12.9 standards for maximum torque capabilities. FSR24-5/8"-13MM-SS is made from 303 stainless steel for increased torque capacity. It is machined from bar stock that is sourced exclusively from North American mills and RoHS3 and REACH compliant. FSR24-5/8"-13MM-SS is manufactured in our Marlborough, MA factory under strict controls using proprietary processes.

**Product Specifications** 

i roddot opcomodions			
Bore (B1)	0.6250 in	Small Bore (B2)	13 mm
B1 Max Shaft Penetration	1.075 in (27.3 mm)	B2 Max Shaft Penetration	1.075 in (27.3 mm)
Outer Diameter (OD)	1.500 in (38.1 mm)	Bore Tolerance	+0.001 in / -0.000 in (+0.025 mm / -0.000 mm)
Length (L)	2.250 in (57.2 mm)	Recommended Shaft Tolerance	+0.0000 / -0.0005 " (+0.000 / -0.013 mm)
Forged Set Screw	M6	Screw Material	Alloy Steel
Hex Wrench Size	3.0 mm	Screw Finish	Black Oxide
Seating Torque	7.2 Nm	Number of Screws	4 ea
Dynamic Torque Reversing	43.75 lb-in (4.94 Nm)	Angular Misalignment	3°
Dynamic Torque Non-Reversing	87.5 lb-in (9.89 Nm)	Parallel Misalignment	0.030 in (0.76 mm)
Static Torque	175 lb-in (19.78 Nm)	Axial Motion	0.015 in (0.38 mm)
Torsional Stiffness	0.031 Deg/lb-in (0.27 Deg/Nm)	Moment of Inertia	0.2814 lb-in <sup>2</sup> , 83.407 x10 <sup>-6</sup> kg-m <sup>2</sup>
Maximum Speed	6,000 RPM	Full Bearing Support Required?	Yes
Zero-Backlash?	Yes	Torque Wrench	TW:BT-4C-3/8-64
Recommended Hex Key	Metric Hex Keys	Material Specification	Type 303 Austenitic, Non-Magnetic Bar
Temperature	-40°F to 350°F (-40°C to 176°C)	Finish Specification	Bright, No Plating
Manufacturer	Ruland Manufacturing	Country of Origin	USA
Weight (lbs)	0.842200	UPC	634529195765
Tariff Code	8483.60.8000	UNSPC	31163003
Note 1	Torque ratings are at maximum misalignment.		
Note 2	Performance ratings are for guidance only. The user must determine suitability for a particular application.		
Note 3	Torque ratings for the couplings are based on the physical limitations/failure point of the machined beams. Under normal/typical conditions the hubs are capable of holding up to the rated torque of the machined beams. In some cases, especially when the smallest standard bores are used or where shafts are undersized, slippage on the shaft is possible below the rated torque of the machined beams. Keyways are available to provide additional torque capacity in the shaft/hub connection when required. Please consult technical support for more assistance.		
Prop 65	▲WARNING This product can expose you to chemicals including Ethylene Thiourea and Nickel (metallic),		

known to the State of California to cause cancer, and Ethylene Thiourea known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="https://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>.

## **Installation Instructions**

- 1. Align the bores of the FSR24-5/8"-13MM-SS six beam coupling on the shafts that are to be joined and determine if the misalignment parameters are within the limits of the coupling. (*Angular Misialignment*: 3°, *Parallel Misalignment*: 0.030 in (0.76 mm), *Axial Motion*: 0.015 in (0.38 mm))
- 2. Fully tighten the M6 screws on one hub to the recommended seating torque of 7.2 Nm using a 3.0 mm hex torque wrench.
- 3. Before tightening the screws on the second hub, rotate the coupling by hand to allow it to reach its free length.
- 4. Tighten the screws on the second hub to the recommended seating torque. Make sure the coupling remains axially relaxed and the misalignment angle remains centered along the length of the coupling.
- 5. The shafts may extend into the relieved portion of the bore as long as it does not exceed the shaft penetration length of 1.075 in (27.3 mm).