




## BC26-5/8"-11MM-A

Ruland BC26-5/8"-11MM-A, 5/8" x 11mm Bellows Coupling, Aluminum, Clamp Style, 1.625" (41.3mm) OD, 2.035" (51.7mm) Length





## **Description**

Ruland BC26-5/8"-11MM-A is a clamp bellows coupling with 0.6250" x 11mm bores, 1.625" (41.3mm) OD, and 2.035" (51.7mm) length. It is zero-backlash and has a balanced design for reduced vibration at high speeds. BC26-5/8"-11MM-A is comprised of two anodized aluminum hubs and a stainless steel bellows. The bellows are able to flex while remaining rigid under torsional loads allowing for all types of misalignment to be accommodated. This bellows coupling is lightweight and has low inertia making it suitable for applications with speeds up to 10,000 RPM. Hardware is metric and tests beyond DIN 912 12.9 standards for maximum torque capabilities. Ruland BC26-5/8"-11MM-A has four convolutions allowing for high torsional rigidity and making it an excellent fit for precise positioning stepper servo applications as well as encoders. It is machined from solid bar stock that is sourced exclusively from North American mills and RoHS3 and REACH compliant. BC26-5/8"-11MM-A is carefully manufactured in our Marlborough, MA factory under strict controls using proprietary processes.

I	)	r٥	d	ш	cf	٩	'n	ec	ifi	ca	tid	on	S

r roduct opecifications							
Bore (B1)	0.6250 in	Small Bore (B2)	11 mm				
B1 Max Shaft Penetration	0.946 in (24.0 mm)	B2 Max Shaft Penetration	0.946 in (24.0 mm)				
Outer Diameter (OD)	1.625 in (41.3 mm)	Bore Tolerance	+0.001 in / -0.000 in (+0.03 mm / -0.00 mm)				
Length (L)	2.035 in (51.7 mm)	Length Tolerance	+/- 0.030 in (0.76 mm)				
Hub Width (LH)	0.710 in (18.05 mm)	Recommended Shaft Tolerance	+0.0000 / -0.0005 " (+0.000 / -0.013 mm)				
Forged Clamp Screw	M4	Screw Material	Alloy Steel				
Hex Wrench Size	3.0 mm	Screw Finish	Black Oxide				
Seating Torque	4.6 Nm	Number of Screws	2 ea				
Dynamic Torque Reversing	62.5 lb-in (7.00 Nm)	Angular Misalignment	2.0°				
<b>Dynamic Torque Non-Reversing</b>	125 lb-in (14.00 Nm)	Parallel Misalignment	0.010 in (0.25 mm)				
Static Torque	250 lb-in (28.0 Nm)	Axial Motion	0.020 in (0.51 mm)				
Torsional Stiffness	550 lb-in/Deg (63 Nm/Deg)	Moment of Inertia	0.105242 lb-in <sup>2</sup> , 30.798 x10 <sup>-6</sup> kg-m <sup>2</sup>				
Maximum Speed	10,000 RPM	Full Bearing Support Required?	Yes				
Zero-Backlash?	Yes	Balanced Design	Yes				
Torque Wrench	TW:BT-1R-1/4-41.0	Recommended Hex Key	Metric Hex Keys				
Material Specification	Hubs: 2024-T351 Aluminum Bar Bellows: Type 321 Stainless Steel	Temperature	-40°F to 200°F (-40°C to 93°C)				
Finish Specification	Sulfuric Anodized MIL-A-8625 Type II, Class 2 and ASTM B580 Type B Black Anodize	Bellows Attachment Method	Ероху				
Manufacturer	Ruland Manufacturing	Country of Origin	USA				
Weight (lbs)	0.287900	UPC	634529141502				
Tariff Code	8483.60.8000	UNSPC	31163018				
Note 1	Stainless steel hubs are available upon request.						
Note 2	Torque ratings are at maximum misalignment.						
Note 3	Performance ratings are for guidance only. The user must determine suitability for a particular application.						
Note 4							

torque capacity in the shaft/hub connection when required. Please consult technical support for more assistance.

## Prop 65

MARNING This product can expose you to chemicals including Ethylene Thiourea and Nickel (metallic), known to the State of California to cause cancer, and Bisphenol A and Ethylene Thiourea, known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="https://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>.

## **Installation Instructions**

- 1. Align the bores of the BC26-5/8"-11MM-A bellows coupling on the shafts that are to be joined and determine if the misalignment parameters are within the limits of the coupling. (*Angular Misialignment*: 2.0°, *Parallel Misalignment*: 0.010 in (0.25 mm), *Axial Motion*: 0.020 in (0.50 mm))
- 2. Fully tighten the M4 screw on the first hub to the recommended seating torque of 4.6 Nm using a 3.0 mm hex torque wrench.
- 3. Before tightening the screw on the second hub, rotate the coupling by hand to allow it to reach its free length.
- 4. Tighten the screw on the second hub to the recommended seating torque. Make sure the coupling remains axially relaxed and the misalignment angle remains centered along the length of the coupling.
- 5. The shafts may extend into the relieved portion of the bore as long as it does not exceed the shaft penetration length of 0.946 in (24.0 mm).