




MDCSK51-19-13-A

Ruland MDCSK51-19-13-A, 19mm x 13mm Single Disc Coupling, Aluminum, Clamp Style With Keyway, 50.8mm OD, 46.1mm Length





Description

Ruland MDCSK51-19-13-A is a clamp single disc coupling with 19mm x 13mm bores, 50.8mm OD, 46.1mm length, and 6mm x 5mm keyways. It is zero-backlash and has a balanced design for reduced vibration at high speeds. The single disc design is comprised of two anodized aluminum hubs and two sets of thin stainless steel disc springs which can accommodate angular misalignment and axial motion, however does not allow for any parallel misalignment. MDCSK51-19-13-A is lightweight and has low inertia making it well suited for applications with speeds up to 10,000 RPM. Hardware is metric and tests beyond DIN 912 12.9 standards for maximum torque capabilities. Ruland manufactures MDCSK51-19-13-A to be torisionally rigid and an excellent fit for precise positioning stepper servo applications commonly found in semiconductor, solar, printing, machine tool, and test and measurement systems. It is machined from solid bar stock that is sourced exclusively from North American mills and RoHS3 and REACH compliant. MDCSK51-19-13-A is manufactured in our Marlborough, MA factory under strict controls using proprietary processes.

Product Specifications

| D (D4) | | | |
|------------------------------------------------------------|---------------------------------------------------------------------------------------------------|------------------------------|----------------------------------------------------------------------------|
| Bore (B1) | 19 mm | Small Bore (B2) | 13 mm |
| Keyway (K1) | 6 mm | Keyway (K2) | 5 mm |
| B1 Max Shaft Penetration | 22.2 mm | B2 Max Shaft Penetration | 22.2 mm |
| Outer Diameter (OD) | 50.8 mm | Bore Tolerance | +0.03 mm / -0.00 mm |
| Length (L) | 46.1 mm | Hub Width (LH) | 20.6 mm |
| Recommended Shaft Tolerance | +0.000 mm / -0.013 mm | Forged Clamp Screw | M5 |
| Screw Material | Alloy Steel | Hex Wrench Size | 4.0 mm |
| Screw Finish | Black Oxide | Seating Torque | 9.5 Nm |
| Number of Screws | 2 ea | Dynamic Torque Reversing | 9.90 Nm |
| Angular Misalignment | 1.0° | Dynamic Torque Non-Reversing | 19.80 Nm |
| Parallel Misalignment | 0.00 mm | Static Torque | 39.6 Nm |
| Axial Motion | 0.32 mm | Torsional Stiffness | 98.0 Nm/Deg |
| Moment of Inertia | 7.439 x 10 ⁻⁵ kg-m ² | Maximum Speed | 10,000 RPM |
| Zero-Backlash? | Yes | Balanced Design | Yes |
| Torque Wrench | TW:BT-4C-3/8-86 | Recommended Hex Key | Metric Hex Keys |
| Full Bearing Support Required? | Yes | Material Specification | Hubs: 2024-T351 Aluminum Bar, Disc Springs: Type 302 Stainless Steel |
| Temperature | -40°F to 200°F (-40°C to 93°C) | Finish Specification | Sulfuric Anodized MIL-A-8625 Type II, Class 2 and ASTM B580 Type B |
| | | | Black Anodize |
| Manufacturer | Ruland Manufacturing | Country of Origin | Black Anodize USA |
| | Ruland Manufacturing 0.460400 | Country of Origin UPC | |
| Weight (lbs) | | | USA |
| Weight (lbs) Tariff Code | 0.460400 | UPC UNSPC | USA 634529204191 |
| Weight (lbs) Tariff Code Note 1 | 0.460400 8483.60.8000 | UPC UNSPC upon request. | USA 634529204191 |
| Manufacturer Weight (lbs) Tariff Code Note 1 Note 2 Note 3 | 0.460400 8483.60.8000 Stainless steel hubs are available Torque ratings are at maximum m | UPC UNSPC upon request. | USA 634529204191 31163008 |

torque capacity in the shaft/hub connection when required. Please consult technical support for more assistance.

Prop 65

MARNING This product can expose you to chemicals including Ethylene Thiourea and Nickel (metallic), known to the State of California to cause cancer, and Ethylene Thiourea known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

Installation Instructions

- Align the bores of the MDCSK51-19-13-A single disc coupling on the shafts that are to be joined and determine if the misalignment parameters are within the limits of the coupling. (*Angular Misialignment*: 1.0°, *Parallel Misalignment*: 0.00 mm, *Axial Motion*: 0.32 mm)
- 2. Fully tighten the M5 screw on the first hub to the recommended seating torque of 9.5 Nm using a 4.0 mm hex torque wrench.
- 3. Before tightening the screw on the second hub, rotate the coupling by hand to allow it to reach its free length.
- 4. Tighten the screw on the second hub to the recommended seating torque. Make sure the coupling remains axially relaxed and the misalignment angle remains centered along the length of the coupling.
- 5. The shafts may extend into the relieved portion of the bore as long as it does not exceed the shaft penetration length of 22.2 mm.