




# **MDCDE15-3-3-A**

Ruland MDCDE15-3-3-A, 3mm x 3mm Double Disc Coupling, Aluminum, Clamp Style, Electrically Isolating, 15.0mm OD, 23.8mm Length





## **Description**

Ruland MDCDE15-3-3-A is an electrically isolating clamp double disc coupling with 3mm x 3mm bores, 15.0mm OD, and 23.8mm length. It is zero-backlash and has a balanced design for reduced vibration at high speeds. The double disc design is comprised of two anodized aluminum hubs, two sets of thin stainless steel disc springs, and an acetal center spacer allowing each disc to bend individually and accommodate all types of misalignment. The acetal center spacer isolates the two hubs preventing the incidental transfer of current from the motor to the driven component or vice versa. MDCDE15-3-3-A is lightweight and has low inertia making it well suited for applications with speeds up to 10,000 RPM. Hardware is metric and tests beyond DIN 912 12.9 standards for maximum torque capabilities. Ruland manufactures MDCDE15-3-3-A to be torisionally rigid and an excellent fit for precise positioning stepper servo applications commonly found in semiconductor, solar, printing, machine tool, and test and measurement systems. It is machined from solid bar stock that is sourced exclusively from North American mills and RoHS3 and REACH compliant. MDCDE15-3-3-A is manufactured in our Marlborough, MA factory under strict controls using proprietary processes.

 	uve	OPC	 ations

r roduct opecifications					
Bore (B1)	3 mm	Small Bore (B2)	3 mm		
B1 Max Shaft Penetration	11.6 mm	B2 Max Shaft Penetration	11.6 mm		
Outer Diameter (OD)	15.0 mm	Bore Tolerance	+0.03 mm / -0.00 mm		
Length (L)	23.8 mm	Hub Width (LH)	8.3 mm		
Recommended Shaft Tolerance	+0.000 mm / -0.013 mm	Forged Clamp Screw	M2		
Screw Material	Alloy Steel	Hex Wrench Size	1.5 mm		
Screw Finish	Black Oxide	Seating Torque	0.6 Nm		
Number of Screws	2 ea	Dynamic Torque Reversing	0.43 Nm		
Angular Misalignment	1.0°	<b>Dynamic Torque Non-Reversing</b>	0.85 Nm		
Parallel Misalignment	0.05 mm	Static Torque	1.7 Nm		
Axial Motion	0.10 mm	Torsional Stiffness	3.0 Nm/Deg		
Moment of Inertia	2.661 x 10 <sup>-7</sup> kg-m <sup>2</sup>	Maximum Speed	10,000 RPM		
Full Bearing Support Required?	Yes	Zero-Backlash?	Yes		
Balanced Design	Yes	Torque Wrench	TW:BT-1R-1/4-5.3		
Recommended Hex Key	Metric Hex Keys	Material Specification	Hubs: 2024-T351 Bar, Disc Springs Type 302 Stainless Steel, Center Spacer: Acetal		
Temperature	-10°F to 150°F (-23°C to 65°C)	Finish Specification	Sulfuric Anodized MIL-A-8625 Type II, Class 2 and ASTM B580 Type B Black Anodize		
Manufacturer	Ruland Manufacturing	Country of Origin	USA		
Weight (lbs)	0.019600	UPC	634529089149		
Tariff Code	8483.60.8000	UNSPC	31163008		
Note 1	Stainless steel hubs are available upon request.				
Note 2	Torque ratings are at maximum misalignment.				
Note 3	Performance ratings are for guidance only. The user must determine suitability for a particular application.				
Note 4	Torque ratings for the couplings are based on the physical limitations/failure point of the disc springs. Under normal/typical conditions the hubs are capable of holding up to the rated torque of the disc springs. In some cases, especially when the smallest standard bores are used or where shafts are undersized, slippage on the shaft is possible below the rated torque of the disc springs. Keyways are available to provide additional torque capacity in the shaft/hub connection when required. Please consult technical support for more				

#### assistance.

### Prop 65

**MARNING** This product can expose you to chemicals including Ethylene Thiourea and Nickel (metallic), known to the State of California to cause cancer, and Ethylene Thiourea known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="https://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>.

#### **Installation Instructions**

- Align the bores of the MDCDE15-3-3-A double disc coupling on the shafts that are to be joined and determine if the misalignment parameters are within the limits of the coupling. (*Angular Misialignment*: 1.0°, *Parallel Misalignment*: 0.05 mm, *Axial Motion*: 0.10 mm)
- 2. Fully tighten the M2 screw on the first hub to the recommended seating torque of 0.6 Nm using a 1.5 mm hex torque wrench.
- 3. Before tightening the screw on the second hub, rotate the coupling by hand to allow it to reach its free length.
- 4. Tighten the screw on the second hub to the recommended seating torque. Make sure the coupling remains axially relaxed and the misalignment angle remains centered along the length of the coupling.
- 5. The shafts may extend into the relieved portion of the bore as long as it does not exceed the shaft penetration length of 11.6 mm.