

# **GL040–0223** BOWMAN<sup>®</sup> *Signature Series* – Glove Box Dispenser – Quad



# **Related Products (each sold separately):**

 GL040-0233 : BOWMAN<sup>®</sup> Signature Series - Glove Box Dispenser -Quad, Cherry Fauxwood ABS Plastic (shown below)

### **Product Description:**

- Glove Box Dispenser Quad with Dividers
- Holds four boxes of gloves
- Three-way keyholes for vertical or horizontal wall mounting
- BOWMAN<sup>®</sup> Signature Series Maple Fauxwood ABS Plastic

### Primary Area for Product Usage:

Anywhere gloves are needed

### Dispenses:

- Box(es) no larger than 5.50"W x 10.00"H x 3.75"D (14.0 cm x 25.4 cm x 9.5 cm)
- Box(es) no smaller than 4.50"W x 9.00"H x 3.00"D (11.4 cm x 22.9 cm x 7.6 cm)


#### Package Specifications:

- Package Quantity: 4 per case
- 26"L x 11"W x 8"H (66.0 cm x 27.9 cm x 20.3 cm)
- 10.0 lbs (4.5 kg) approximated

**Product Specifications** (overall external dimensions):

- 22.63"W x 10.13"H x 4.00"D (57.5 cm x 25.7 cm x 10.2 cm)
- 1.9 lbs (0.8 kg) approximated

Mounting Specifications:









# Installation

Always mount dispensers securely prior to loading with product.



 Mount securely to a wall with screws approved and supplied by building maintenance.



# Parts included:

• Dispenser

## **Tools Required:**

No tools required to assemble dispenser

Care and Construction Fauxwood ABS Plastic

# **Material Characteristics**

Designed for Long-Term, Heavy-Duty Applications

The combination of copolymers (Acrylonitrile, Butadiene, and Styrene) gives ABS an excellent combination of strength, rigidity, and toughness. The fauxwood finish is ARVINYL laminate created from a semi-rigid film.

ABS is chemical and stress-crack resistant. It is tough, dimensionally stable, and will hold up to long-term use. To ensure product longevity, fauxwood products should not be mounted in very hot or cold areas.

# Care and Cleaning

Use mild soap and water to clean. Petroleum-based oils, solvents, and paints should not be used.

Standard hospital cleaning supplies are approved for use on our ABS plastic products.

GL040-0223 - Installation/Characteristics & Care Information subject to change without notice. Dimensions are approximate. (Not to scale)

ion subject to change without notice. Dimensions are approximate. (Not to scale) 800.962.4660 • www.BowmanDis ©2019 BOWMAN® Manufacturing Company, Inc. All Rights Reserved. Product specifications subject to change without notification. Consumables not included. GL0400223TDSa