




FCR10-1/4"-6MM-SS

Ruland FCR10-1/4"-6MM-SS, 1/4" x 6mm Six Beam Coupling, Stainless Steel, Clamp Style, 0.625" (15.9mm) OD, 1.000" (25.4mm) Length





Description

Ruland FCR10-1/4"-6MM-SS is a clamp style six beam coupling with 0.2500" x 6mm bores, 0.625" (15.9mm) OD, and 1.000" (25.4mm) length. It is machined from a single piece of material and features two sets of three spiral cuts. This gives it higher torque capacity, lower windup, and larger body sizes than single or four beam couplings and allows for use in light duty power transmission applications such as coupling a servo motor to a lead screw. FCR10-1/4"-6MM-SS is zero-backlash and has a balanced design for reduced vibration at high speeds of up to 6,000 RPM. Ruland supplies this spiral coupling with Nypatch® anti-vibration hardware that allows for even seating of the screw, repeated screw installations, prevents galling, and maintains high holding power. All hardware is metric and tests beyond DIN 912 12.9 standards for maximum torque capabilities. FCR10-1/4"-6MM-SS is made from 303 stainless steel for increased torque capacity. It is machined from bar stock that is sourced exclusively from North American mills and RoHS3 and REACH compliant. FCR10-1/4"-6MM-SS is manufactured in our Marlborough, MA factory under strict controls using proprietary processes.

Product Specifications

i roduct opcomeations			
Bore (B1)	0.2500 in	Small Bore (B2)	6 mm
B1 Max Shaft Penetration	0.483 in (12.3 mm)	B2 Max Shaft Penetration	0.483 in (12.3 mm)
Outer Diameter (OD)	0.625 in (15.9 mm)	Bore Tolerance	+0.001 in / -0.000 in (+0.025 mm / -0.000 mm)
Length (L)	1.000 in (25.4 mm)	Clearance Diameter (C) MAX	0.796 in (20.22 mm)
Recommended Shaft Tolerance	+0.0000 / -0.0005 " (+0.000 / -0.013 mm)	3 Cap Screw	M2.5
Screw Material	Stainless Steel	Hex Wrench Size	2.0 mm
Screw Finish	Black Oxide	Seating Torque	1.21 Nm
Number of Screws	2 ea	Dynamic Torque Reversing	4.5 lb-in (0.51 Nm)
Angular Misalignment	3°	Dynamic Torque Non-Reversing	9 lb-in (1.02 Nm)
Parallel Misalignment	0.008 in (0.20 mm)	Static Torque	18 lb-in (2.03 Nm)
Axial Motion	0.005 in (0.13 mm)	Torsional Stiffness	0.088 Deg/lb-in (0.78 Deg/Nm)
Moment of Inertia	0.0037 lb-in ² , 1.097 x10 ⁻⁶ kg-m ²	Maximum Speed	6,000 RPM
Full Bearing Support Required?	Yes	Zero-Backlash?	Yes
Balanced Design	Yes	Torque Wrench	TW:BT-1R-1/4-10.7
Recommended Hex Key	Metric Hex Keys	Material Specification	Type 303 Austenitic, Non-Magnetic Bar
Temperature	-40°F to 350°F (-40°C to 176°C)	Finish Specification	Bright, No Plating
Manufacturer	Ruland Manufacturing	Country of Origin	USA
Weight (lbs)	0.061000	UPC	634529192634
Tariff Code	8483.60.8000	UNSPC	31163003
Note 1	Torque ratings are at maximum misalignment.		
Note 2	Performance ratings are for guidance only. The user must determine suitability for a particular application.		
Note 3	Torque ratings for the couplings are based on the physical limitations/failure point of the machined beams. Under normal/typical conditions the hubs are capable of holding up to the rated torque of the machined beams. In some cases, especially when the smallest standard bores are used or where shafts are undersized, slippage on the shaft is possible below the rated torque of the machined beams. Keyways are available to provide additional torque capacity in the shaft/hub connection when required. Please consult technical support for more assistance.		
Prop 65	▲ WARNING This product can expose you to chemicals including Ethylene Thiourea and Nickel (metallic),		

Installation Instructions

- 1. Align the bores of the FCR10-1/4"-6MM-SS six beam coupling on the shafts that are to be joined and determine if the misalignment parameters are within the limits of the coupling. (*Angular Misialignment*: 3°, *Parallel Misalignment*: 0.008 in (0.20 mm), *Axial Motion*: 0.005 in (0.13 mm))
- 2. Fully tighten the M2.5 screw on one hub to the recommended seating torque of 1.21 Nm using a 2.0 mm hex torque wrench.
- 3. Before tightening the screws on the second hub, rotate the coupling by hand to allow it to reach its free length.
- 4. Tighten the screws on the second hub to the recommended seating torque. Make sure the coupling remains axially relaxed and the misalignment angle remains centered along the length of the coupling.
- 5. The shafts may extend into the relieved portion of the bore as long as it does not exceed the shaft penetration length of 0.483 in (12.3 mm).