# GL020-0223

## BOWMAN® Signature Series - Glove Box Dispenser - Double



GL020-0111: Glove Dispenser - Double, PETG Plastic (shown below)

GL020-0233: Glove Dispenser - Double, Cherry Fauxwood ABS

### **Product Description:**

- · Glove Box Dispenser Double with Divider
- · Holds two boxes of gloves
- · Three-way keyholes for vertical or horizontal wall mounting
- BOWMAN® Signature Series Maple Fauxwood ABS Plastic

#### Primary Area for Product Usage:

· Anywhere gloves are needed

#### Dispenses:

- Box(es) no larger than 5.50"W x 10.00"H x 3.75"D (14.0 cm x 25.4 cm x 9.5 cm)
- Box(es) no smaller than 4.50"W x 9.00"H x 3.00"D (11.4 cm x 22.9 cm x 7.6 cm)

### Package Specifications:


- Package Quantity: 6 per case
- 16"L x 12"W x 12"H (40.6 cm x 30.5 cm x 30.5 cm)
- 9.0 lbs (4.1 kg) approximated

### **Product Specifications** (overall external dimensions):

- 11.38"W x 10.13"H x 4.00"D (28.9 cm x 25.7 cm x 10.2 cm)
- 1.2 lbs (0.5 kg) approximated

### **Mounting Specifications:**





Related Products (each sold separately):

Plastic


### GL020-0223


### **BOWMAN®** Signature Series - Glove Box Dispenser - Double

Installation Instructions/Characteristics & Care

### Installation

Always mount dispensers securely prior to loading with product.





### Parts included:

Dispenser

### **Tools Required:**

No tools required to assemble dispenser

### Care and Construction Fauxwood ABS Plastic

### **Material Characteristics**

### Designed for Long-Term, Heavy-Duty **Applications**

The combination of copolymers (Acrylonitrile, Butadiene, and Styrene) gives ABS an excellent combination of strength, rigidity, and toughness. The fauxwood finish is ARVINYL laminate created from a semi-rigid film.

ABS is chemical and stress-crack resistant. It is tough, dimensionally stable, and will hold up to long-term use. To ensure product longevity. fauxwood products should not be mounted in very hot or cold areas.

Use mild soap and water to clean. Petroleum-based oils, solvents, and paints should not be used.

Standard hospital cleaning supplies are approved for use on our ABS plastic products.