




## PSR18-7MM-1/4"-A

Ruland PSR18-7MM-1/4"-A, 7mm x 1/4" Four Beam Coupling, Aluminum, Set Screw Style, 1.125" (28.6mm) OD, 1.500" (38.1mm) Length





## **Description**

Ruland PSR18-7MM-1/4"-A is a set screw style four beam coupling with 7mm x 0.2500" bores, 1.125" (28.6mm) OD, and 1.500" (38.1mm) length. It is machined from a single piece of material and feature two sets of two spiral cuts. This gives it higher torque capacity, lower windup, and larger body sizes than single beam couplings. PSR18-7MM-1/4"-A is zero-backlash and has a balanced design for reduced vibration at high speeds of up to 6,000 RPM. This four beam spiral coupling is zero-backlash and has a balanced design for reduced vibration at high speeds of up to 6,000 RPM. All hardware is metric and tests beyond DIN 912 12.9 standards for maximum torque capabilities. PSR18-7MM-1/4"-A is made from 7075 aluminum for lightweight and low inertia. It is machined from bar stock that is sourced exclusively from North American mills and RoHS3 and REACH compliant. PSR18-7MM-1/4"-A is manufactured in our Marlborough, MA factory under strict controls using proprietary processes.

**Product Specifications** 

i roduct opecifications			
Bore (B1)	7 mm	Small Bore (B2)	0.2500 in
B1 Max Shaft Penetration	0.695 in (17.6 mm)	B2 Max Shaft Penetration	0.695 in (17.6 mm)
Outer Diameter (OD)	1.125 in (28.6 mm)	Bore Tolerance	+0.001 in / -0.000 in (+0.025 mm /
			-0.000 mm)
Length (L)	1.500 in (38.1 mm)	Recommended Shaft Tolerance	+0.0000 / -0.0005 " (+0.000 / -0.013
			mm)
Forged Set Screw	M5	Screw Material	Alloy Steel
Hex Wrench Size	2.5 mm	Screw Finish	Black Oxide
Seating Torque	4 Nm	Number of Screws	4 ea
Dynamic Torque Reversing	11.75 lb-in (1.33 Nm)	Angular Misalignment	3°
Dynamic Torque Non-Reversing	23.5 lb-in (2.66 Nm)	Parallel Misalignment	0.015 in (0.38 mm)
Static Torque	47.0 lb-in (5.31 Nm)	Axial Motion	0.010 in (0.25 mm)
Torsional Stiffness	0.097 Deg/lb-in (0.86 Deg/Nm)	Moment of Inertia	0.0217 lb-in <sup>2</sup> , 6.349 x10 <sup>-6</sup> kg-m <sup>2</sup>
Maximum Speed	6,000 RPM	Full Bearing Support Required?	Yes
Zero-Backlash?	Yes	Torque Wrench	TW:BT-1R-1/4-35.0
Recommended Hex Key	Metric Hex Keys	Material Specification	7075-T651 Extruded and Drawn
			Aluminum Bar
Temperature	-40°F to 225°F (-40°C to 107°C)	Finish Specification	Bright, No Plating
Manufacturer	Ruland Manufacturing	Country of Origin	USA
Weight (lbs)	0.121200	UPC	634529198780
Tariff Code	8483.60.8000	UNSPC	31163003
Note 1	Torque ratings are at maximum misalignment.		
Note 2	Performance ratings are for guidance only. The user must determine suitability for a particular application.		
Note 3	Torque ratings for the couplings are based on the physical limitations/failure point of the machined beams. Under normal/typical conditions the hubs are capable of holding up to the rated torque of the machined beams. In some cases, especially when the smallest standard bores are used or where shafts are undersized, slippage on the shaft is possible below the rated torque of the machined beams. Keyways are available to provide additional torque capacity in the shaft/hub connection when required. Please consult		
Draw CF	technical support for more assistance.  MARNING This product can expose you to the chemical Ethylene Thiourea, known to the State of		
Prop 65	WARNING This product can exp	pose you to the chemical Ethylene Th	niourea, known to the State of

California to cause cancer and birth defects or other reproductive harm. For more information go to

Ruland Manufacturing Co., Inc.

www.P65Warnings.ca.gov.

## **Installation Instructions**

- 1. Align the bores of the PSR18-7MM-1/4"-A four beam coupling on the shafts that are to be joined and determine if the misalignment parameters are within the limits of the coupling. (*Angular Misialignment*: 3°, *Parallel Misalignment*: 0.015 in (0.38 mm), *Axial Motion*: 0.010 in (0.25 mm))
- 2. Fully tighten the M5 screws on one hub to the recommended seating torque of 4 Nm using a 2.5 mm hex torque wrench.
- 3. Before tightening the screws on the second hub, rotate the coupling by hand to allow it to reach its free length.
- Tighten the screws on the second hub to the recommended seating torque. Make sure the coupling remains axially relaxed and the misalignment angle remains centered along the length of the coupling.
- 5. The shafts may extend into the relieved portion of the bore as long as it does not exceed the shaft penetration length of 0.695 in (17.6 mm).