




## MDCDK41-15-10-A

Ruland MDCDK41-15-10-A, 15mm x 10mm Double Disc Coupling, Aluminum, Clamp Style With Keyway, 41.3mm OD, 55.0mm Length





## **Description**

Ruland MDCDK41-15-10-A is a clamp double disc coupling with 15mm x 10mm bores, 41.3mm OD, 55.0mm length, and 5mm x 3mm keyways. It is zero-backlash and has a balanced design for reduced vibration at high speeds. The double disc design is comprised of two anodized aluminum hubs, two sets of thin stainless steel disc springs, and a center spacer allowing each disc to bend individually and accommodate all types of misalignment. MDCDK41-15-10-A is lightweight and has low inertia making it well suited for applications with speeds up to 10,000 RPM. Hardware is metric and tests beyond DIN 912 12.9 standards for maximum torque capabilities. Ruland manufactures MDCDK41-15-10-A to be torisionally rigid and an excellent fit for precise positioning stepper servo applications commonly found in semiconductor, solar, printing, machine tool, and test and measurement systems. It is machined from solid bar stock that is sourced exclusively from North American mills and RoHS3 and REACH compliant. MDCDK41-15-10-A is manufactured in our Marlborough, MA factory under strict controls using proprietary processes.

			-	•			
ப	ra	AII.	IC+	SINO	CITI	へつきょん	ne
	ıvı	uч	JUL	Suc		catio	JI IS

Bore (B1)	15 mm	Small Bore (B2)	10 mm			
Keyway (K1)	5 mm	Keyway (K2)	3 mm			
B1 Max Shaft Penetration	26.1 mm	B2 Max Shaft Penetration	26.1 mm			
Outer Diameter (OD)	41.3 mm	Bore Tolerance	+0.03 mm / -0.00 mm			
Length (L)	55.0 mm	Hub Width (LH)	18.0 mm			
Recommended Shaft Tolerance	+0.000 mm / -0.013 mm	Forged Clamp Screw	M4			
Screw Material	Alloy Steel	Hex Wrench Size	3.0 mm			
Screw Finish	Black Oxide	Seating Torque	4.6 Nm			
Number of Screws	2 ea	Dynamic Torque Reversing	5.08 Nm			
Angular Misalignment	2.0°	Dynamic Torque Non-Reversing	10.15 Nm			
Parallel Misalignment	0.25 mm	Static Torque	20.3 Nm			
Axial Motion	0.51 mm	Torsional Stiffness	42.4 Nm/Deg			
Moment of Inertia	3.8373 x 10 <sup>-5</sup> kg-m <sup>2</sup>	Maximum Speed	10,000 RPM			
Zero-Backlash?	Yes	Balanced Design	Yes			
Torque Wrench	TW:BT-1R-1/4-41.0	Recommended Hex Key	Metric Hex Keys			
Full Bearing Support Required?	Yes	Material Specification	Hubs and Center Spacer: 2024-T351 Aluminum Bar Disc Springs: Type 302 Stainless Steel			
Temperature	-40°F to 200°F (-40°C to 93°C)	Finish Specification	Sulfuric Anodized MIL-A-8625 Type II, Class 2 and ASTM B580 Type B Black Anodize			
Manufacturer	Ruland Manufacturing	Country of Origin	USA			
Weight (lbs)	0.319100	UPC	634529175422			
Tariff Code	8483.60.8000	UNSPC	31163008			
Note 1	Stainless steel hubs are available upon request.					
Note 2	Torque ratings are at maximum misalignment.					
Note 3	Performance ratings are for guidance only. The user must determine suitability for a particular application.					
Note 4	Torque ratings for the couplings are based on the physical limitations/failure point of the disc springs. Under normal/typical conditions the hubs are capable of holding up to the rated torque of the disc springs. In some cases, especially when the smallest standard bores are used or where shafts are undersized, slippage on the shaft is possible below the rated torque of the disc springs. Keyways are available to provide additional					

torque capacity in the shaft/hub connection when required. Please consult technical support for more assistance.

## Prop 65

**MARNING** This product can expose you to chemicals including Ethylene Thiourea and Nickel (metallic), known to the State of California to cause cancer, and Ethylene Thiourea known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="https://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>.

## **Installation Instructions**

- 1. Align the bores of the MDCDK41-15-10-A double disc coupling on the shafts that are to be joined and determine if the misalignment parameters are within the limits of the coupling. (*Angular Misialignment*: 2.0°, *Parallel Misalignment*: 0.25 mm, *Axial Motion*: 0.51 mm)
- 2. Fully tighten the M4 screw on the first hub to the recommended seating torque of 4.6 Nm using a 3.0 mm hex torque wrench.
- 3. Before tightening the screw on the second hub, rotate the coupling by hand to allow it to reach its free length.
- 4. Tighten the screw on the second hub to the recommended seating torque. Make sure the coupling remains axially relaxed and the misalignment angle remains centered along the length of the coupling.
- 5. The shafts may extend into the relieved portion of the bore as long as it does not exceed the shaft penetration length of 26.1 mm.